



Metric table

Dimensions in: millimeters - inches

1		2		3						d ₃	h ₁	h ₂	
d ₁		d ₂		Length l									
VP	VP-H	VP	VP-H										
20 0.79	-	M 4	-	10 0.39	15 0.59	25 0.98	-	-	-	-	13 0.51	16 0.63	8 0.31
20 0.79	-	M 5	-	10 0.39	15 0.59	20 0.79	25 0.98	-	-	-	13 0.51	16 0.63	8 0.31
20 0.79	-	M 6	-	10 0.39	15 0.59	20 0.79	25 0.98	35 1.38	-	-	13 0.51	16 0.63	8 0.31
30 1.18	-	M 5	-	10 0.39	20 0.79	-	-	-	-	-	17 0.67	24 0.94	11 0.43
30 1.18	-	M 6	-	10 0.39	15 0.59	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	17 0.67	24 0.94	11 0.43
30 1.18	-	M 8	-	15 0.59	20 0.79	25 0.98	30 1.18	35 1.38	45 1.77	60 2.36	17 0.67	24 0.94	11 0.43
-	40 1.57	-	M 6	20 0.79	25 0.98	-	-	-	-	-	21 0.83	28 1.10	13 0.51
-	40 1.57	-	M 8	20 0.79	25 0.98	30 1.18	-	-	-	-	21 0.83	28 1.10	13 0.51
-	50 1.97	-	M 8	25 0.98	30 1.18	40 1.57	50 1.97	60 2.36	-	-	24 0.94	32 1.26	15 0.59
-	50 1.97	-	M 10	25 0.98	30 1.18	40 1.57	-	-	-	-	24 0.94	32 1.26	15 0.59
-	60 2.36	-	M 10	20 0.79	30 1.18	35 1.38	40 1.57	-	-	-	28 1.10	35 1.38	15 0.59
-	60 2.36	-	M 12	40 1.57	50 1.97	60 2.36	80 3.15	-	-	-	28 1.10	35 1.38	15 0.59
-	70 2.76	-	M 12	30 1.18	40 1.57	50 1.97	-	-	-	-	32 1.26	42 1.65	21 0.83
-	90 3.54	-	M 16	60 2.36	70 2.76	-	-	-	-	-	42 1.65	55 2.17	26 1.02

Specification

- Six-lobed knob
Phenolic plastic
 - Temperature resistant up to 300 °F (150 °C)
 - Black, shiny finish
- Threaded stud
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- RoHS compliant

Information

VP and VP-H are economical but durable six-lobed knobs for many applications.

see also...

- *Six-Lobed Knobs VB (Solid Type, with Blind Tapped Insert)* → page 590
- *Six-Lobed Knobs VB-FP (Solid Type, with Through Tapped Insert)* → page 591
- *Six-Lobed Knobs VB-FP-H (Hollow Type, with Through Tapped Insert)* → page 591

How to order (Solid type)	1 Handle diameter d ₁
1 2 3	2 Thread d ₂
VP-20-M6-20	3 Length l
How to order (Hollow type)	1 Handle diameter d ₁
1 2 3	2 Thread d ₂
VP-H-60-M12-50	3 Length l