




4 Type
A Bore filleted on one side

Inch table

1				2		3				Dimensions in: inches / millimeters			
d ₁				d ₂		Length l							
B 0.098	^{+0.0001} / _{+0.0004}	-	-	0.2030	^{+0.0016} / _{+0.0012} ^{+0.0005} / _{+0.0305}	0.5000	-	-	-	-	-	-	-
B 0.098	^{+0.0001} / _{+0.0004}	-	-	5.1562	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	12.7	-	-	-	-	-	-	-
B 0.191	^{+0.0001} / _{+0.0004}	-	-	0.2500	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	0.3750	-	-	-	-	-	-	-
B 0.191	^{+0.0001} / _{+0.0004}	-	-	6.35	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	9.5	-	-	-	-	-	-	-
B 0.25	^{+0.0001} / _{+0.0004}	-	-	0.3125	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	0.3750	-	-	-	-	-	-	-
B 0.25	^{+0.0001} / _{+0.0004}	-	-	7.9375	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	9.5	-	-	-	-	-	-	-
B 0.25	^{+0.0001} / _{+0.0004}	-	-	0.3750	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	0.5000	-	-	-	-	-	-	-
B 0.25	^{+0.0001} / _{+0.0004}	-	-	9.525	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	12.7	-	-	-	-	-	-	-
B 0.25	^{+0.0001} / _{+0.0004}	B 0.252	^{+0.0001} / _{+0.0005}	0.4063	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	0.2500	0.3125	0.3750	0.5000	7.9	9.5	12.7	
B 0.25	^{+0.0001} / _{+0.0004}	B 0.313	^{+0.0001} / _{+0.0005}	10.32	^{+0.0017} / _{+0.0014} ^{+0.0432} / _{+0.0356}	12.7	-	-	-	-	-	-	
B 0.257	^{+0.0001} / _{+0.0005}	-	-	0.5000	^{+0.0017} / _{+0.0014} ^{+0.0432} / _{+0.0356}	12.7	-	-	-	-	-	-	
B 0.257	^{+0.0001} / _{+0.0005}	-	-	12.7	^{+0.0017} / _{+0.0014} ^{+0.0432} / _{+0.0356}		-	-	-	-	-	-	
B 0.375	^{+0.0001} / _{+0.0005}	-	-	0.4063	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	0.3125	-	-	-	-	-	-	
B 0.375	^{+0.0001} / _{+0.0005}	-	-	10.32	^{+0.0016} / _{+0.0012} ^{+0.0406} / _{+0.0305}	7.9	-	-	-	-	-	-	
B 0.375	^{+0.0001} / _{+0.0005}	-	-	0.6250	^{+0.0017} / _{+0.0014} ^{+0.0432} / _{+0.0356}	0.7500	1.0000	0.3750	0.5000	25.4	9.5	12.7	
B 0.375	^{+0.0001} / _{+0.0005}	-	-	15.875	^{+0.0017} / _{+0.0014} ^{+0.0432} / _{+0.0356}	19.1							
B 0.5	^{+0.0001} / _{+0.0005}	-	-	0.7500	^{+0.0018} / _{+0.0015} ^{+0.0457} / _{+0.0381}	1.0000	1.3750	0.5000	-	34.9	12.7	-	
B 0.5	^{+0.0001} / _{+0.0005}	-	-	19.05	^{+0.0018} / _{+0.0015} ^{+0.0457} / _{+0.0381}	25.4							
B 0.625	^{+0.0001} / _{+0.0005}	-	-	0.8750	^{+0.0018} / _{+0.0015} ^{+0.0457} / _{+0.0381}	0.5000	-	-	-	-	-	-	
B 0.625	^{+0.0001} / _{+0.0005}	-	-	22.225	^{+0.0018} / _{+0.0015} ^{+0.0457} / _{+0.0381}	12.7							

Specification

- Steel
- Hardened (HRC 62 ±2)
 - Fit surface d₁ and d₂ precision machined

RoHS

On request

- Other bores d₁
- Other bores d₂
- Other length l

Press-fit drill bushings WN 179 are characterized by the tight dimensional and positional tolerances in connection with the hardened and precision machined surface. As a result, they are suitable for extremely universal use in many applications.

see also...	Page
DIN 179 Press-Fit Drill Bushings (Metric Size)	QVX
GN 172.1 Press-Fit Guide Bushings (with Conical Bore)	QVX
GN 179.1 Press-Fit Guide Bushings (with Conical Bore)	QVX

Technical Information	QVX
ISO Fundamental Tolerances	

How to order	1 Bore d ₁
	2 Diameter d ₂
	3 Length l
	4 Type
WN 179-B0.25-0.3750-0.5000-A	