



Inch | Metric



Specification



Lever body

Plastic, Nylon thermoplastic **KT**

- Glass fiber reinforced
- With molded-in stainless steel inlay
- Operating temperature up to 230 °F (110 °C)
- Color

- Black, RAL 9005, textured finish **● SW**
- Orange, RAL 2004, textured finish **● OS**

Threaded stud / Retaining screw

Steel, zinc plated, blue passivated finish

RoHS

Technical Information Page

Plastic Characteristics	QVX
Strength Values of Screws	QVX

Made in the USA, adjustable levers WN 302.2 have a straight lever parallel to the clamping surface. For some applications this presents an advantage due to limits of space or for visual reasons.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swivelled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...	Page
GN 304 Straight Adjustable Levers (Nylon Plastic, with Steel Threaded Stud Type, with Push Button)	QVX
WN 302 Straight Adjustable Levers (Nylon Plastic, with Steel Insert)	QVX
GN 302 Straight Adjustable Levers (Zinc Die-Cast, Threaded Stud Type)	QVX
WN 304 Straight Adjustable Levers (Nylon Plastic, with Steel Threaded Stud Type, with Push Button)	QVX

How to order (Inch)

WN 302.2-KT-45-10X32-10-SW

1	Material
2	Lever length l_1
3	Thread d_1
4	Thread length l_2
5	Lever color

How to order (Metric)

WN 302.2-KT-78-M10-40-SW

1	Material
2	Lever length l_1
3	Thread d_1
4	Thread length l_2
5	Lever color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4



Inch table

2 **3** **4** Dimensions in: inches / millimeters

l ₁	d ₁	l ₂									d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
		0.39	0.47	0.63	0.79	0.98	1.26	-	-	-						
1.77 45	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.77 45	10 x 24	0.63 16	0.79 20	1.26 32	-	-	-	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.77 45	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	0.87 22	0.14 3.5
2.48 63	1/4 x 20	0.63 16	0.79 20	0.98 25	-	-	-	-	-	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.12 28.5	0.16 4
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.12 28.5	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.87 22.2	1.42 36	0.31 8	1.34 34	0.16 4
3.07 78	1/2 x 13	1.26 32	1.57 40	-	-	-	-	-	-	-	0.63 16	0.87 22.2	1.42 36	0.31 8	1.34 34	0.16 4

Metric table

2 **3** **4** Dimensions in: millimeters / inches

l ₁	d ₁		l ₂							d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
			12	16	20	25	32	40	50						
30 1.18	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	22 0.87	3.5 0.14
30 1.18	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	24.5 0.96	4 0.16	22 0.87	3.5 0.14
45 1.77	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	22 0.87	3.5 0.14
45 1.77	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	24.5 0.96	4 0.16	22 0.87	3.5 0.14
63 2.48	M 6	M 8	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	28.5 1.12	4 0.16
78 3.07	M 8	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	22.2 0.87	36 1.42	8 0.31	34 1.34	4 0.16