Adjustable Levers

Plastic, Tapped Type, with Zinc Plated Steel Components

JW WINCO® A Ganter Company

Inch | Metric





Specification

Lever body

Plastic, Nylon thermoplastic **KT**

- Glass fiber reinforced
- With molded-in stainless steel inlay
- Operating temperature up to 230 °F (110 °C)
- Color
  - Black, RAL 9005, textured finish **SW**
  - Orange, RAL 2004, textured finish **OS**
  - Gray, RAL 7035, textured finish **GS**

Insert / Retaining screw

Stainless steel AISI 303

RoHS

On request

- Special colors and threads

Made in the USA, adjustable levers WN 300.2 are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

All such levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...	Page
WN 300.2 Adjustable Levers (Nylon Plastic, with Zinc Plated Steel Threaded Stud)	QVX
GN 300.2 Adjustable Levers (Zinc Die-Cast, with Zinc Plated Steel Insert)	QVX
WN 300 Adjustable Levers (Nylon Plastic, with Blackened Steel Threaded Stud)	QVX
GN 300 Adjustable Levers (Zinc Die-Cast, with Blackened Steel Insert)	QVX
WN 303 Adjustable Levers (Nylon Plastic, with Push Button)	QVX
GN 303 Adjustable Levers (Zinc Die-Cast, with Push Button)	QVX

Technical Information

Plastic Characteristics QVX

How to order (Inch)

WN 300.2-KT-78-3/8X16-OS

1	Material
2	Lever length l_1
3	Thread d_1
4	Color

How to order (Metric)

WN 300.2-KT-92-M10-GS

1	Material
2	Lever length l_1
3	Thread d_1
4	Color

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

Inch table

Dimensions in: inches / millimeters

l_1	d_1			d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
1.77 45	10 x 32	10 x 24	1/4 x 20	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5	0.35 9
2.48 63	1/4 x 20	5/16 x 18	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4	0.43 11
3.07 78	5/16 x 18	3/8 x 16	-	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4	0.55 14
3.62 92	3/8 x 16	1/2 x 13	-	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65	0.16 4	0.67 17

Metric table

Dimensions in: millimeters / inches

l_1	d_1			d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
30 1.18	M 4	M 5	M 6	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	9 0.35
45 1.77	M 4	M 5	M 6	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14	9 0.35
63 2.48	M 6	M 8	-	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16	11 0.43
78 3.07	M 8	M 10	-	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16	14 0.55
92 3.62	M 10	M 12	-	19 0.75	25.2 0.99	43 1.69	11 0.43	65 2.56	4 0.16	17 0.67