



Specification



- Lever body
Plastic **KT**
Nylon thermoplastic
- Glass fiber reinforced
- With molded-in stainless steel inlay
- Temperature resistant up to 230 °F (110 °C)
- Color
Black, RAL 9005, textured finish **● SW**
Orange, RAL 2004, textured finish **● OS**
Gray, RAL 7035, textured finish **● GS**
- Push button
Nylon plastic **● S**
Black, RAL 9005 **● O**
Orange, RAL 2004 **● G**
Gray, RAL 7035 **● G**
- Threaded stud
Steel, zinc plated, blue passivated finish
- [Plastic Characteristics](#) → page QVX
- [Torque Rating Information](#) → page QVX
- [RoHS compliant](#)

Information

Made in the USA, WN 303.2 adjustable levers with push button are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

All such levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The push button is a design element and allows for effortless release action. However, this design is limited to applications that do not require the lever to be disassembled.

see also...

- [Adjustable Levers WN 303 \(Nylon Plastic, with Push Button, Tapped or Plain Bore Type\)](#) → page QVX
- [Adjustable Levers GN 303.1 \(Zinc Die-Cast, with Push Button, Threaded Stud Type, with Stainless Steel Components\)](#) → page QVX
- [Adjustable Levers WN 303.1 \(Nylon Plastic, with Push Button, Threaded Stud Type, with Stainless Steel Components\)](#) → page QVX
- [Adjustable Levers GN 303 \(Zinc Die-Cast, with Push Button, Threaded Stud Type\)](#) → page QVX

On request

- Special colors

How to order (Inch)	1	Material
	2	Lever length l ₁
	3	Thread d ₁
	4	Thread length l ₂
	5	Lever color
	6	Push button color
 WN 303.2-KT-45-10X32-10-SW-O		

How to order (Metric)	1	Material
	2	Lever length l ₁
	3	Thread d ₁
	4	Thread length l ₂
	5	Lever color
	6	Push button color
 WN 303.2-KT-78-M8-16-GS-S		

Inch table

Dimensions in: inches - *millimeters*

² l ₁	³ d ₁	⁴ l ₂									d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
1.77 45	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
1.77 45	10 x 24	0.63 16	0.79 20	1.26 32	-	-	-	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
1.77 45	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
2.48 63	1/4 x 20	0.63 16	0.79 20	0.98 25	-	-	-	-	-	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
2.48 63	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4

Metric table

Dimensions in: millimeters - *inches*

² l ₁	³ d ₁	⁴ l ₂									d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
30 1.18	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14
30 1.18	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14
45 1.77	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14
45 1.77	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14
63 2.48	M 6	M 8	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	-	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16
78 3.07	M 8	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

