



**Specification**



• Lever body	
Plastic	<b>KT</b>
Nylon thermoplastic	
- Glass fiber reinforced	
- With molded-in stainless steel inlay	
- Temperature resistant up to 230 °F (110 °C)	
• Color	
Black, RAL 9005, textured finish	● <b>SW</b>
Orange, RAL 2004, textured finish	● <b>OS</b>
Gray, RAL 7035, textured finish	● <b>GS</b>
• Push button	
Nylon plastic	
Black, RAL 9005	● <b>S</b>
Orange, RAL 2004	● <b>O</b>
Gray, RAL 7035	● <b>G</b>
• Threaded stud	
Steel, blackened finish	
• <i>Plastic Characteristics</i> → page 2135	
• <i>RoHS compliant</i>	

**Information**

Made in the USA, WN 303 adjustable levers with push button are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

All such levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The push button is a design element and allows for effortless release action. However, this design is limited to applications that do not require the lever to be disassembled.

**see also...**

- *Adjustable Levers WN 303 (Nylon Plastic, with Push Button, Tapped or Plain Bore Type)* → page 444
- *Adjustable Levers GN 303 (Zinc Die-Cast, with Push Button, Threaded Stud Type)* → page 440
- *Adjustable Levers WN 303.1 (Nylon Plastic, with Push Button, Threaded Stud Type, with Stainless Steel Components)* → page 450
- *Adjustable Levers GN 303.1 (Zinc Die-Cast, with Push Button, Threaded Stud Type, with Stainless Steel Components)* → page 442

**On request**

- Special colors, stud lengths, and threads

<p>How to order (Inch)</p> <p style="text-align: center;"> </p> <p style="text-align: center;"><b>WN 303-KT-63-5/16X18-63-OS-O</b></p>	<b>1</b> Material
	<b>2</b> Lever length $l_1$
	<b>3</b> Thread $d_1$
	<b>4</b> Thread length $l_2$
	<b>5</b> Lever color
	<b>6</b> Push button color

<p>How to order (Metric)</p> <p style="text-align: center;"> </p> <p style="text-align: center;"><b>WN 303-KT-78-M8-16-GS-S</b></p>	<b>1</b> Material
	<b>2</b> Lever length $l_1$
	<b>3</b> Thread $d_1$
	<b>4</b> Thread length $l_2$
	<b>5</b> Lever color
	<b>6</b> Push button color

**Inch table**

Dimensions in: inches - millimeters

l <sub>1</sub>	d <sub>1</sub>	l <sub>2</sub>									d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke
		0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-						
1.18 30	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.20 30.5	0.14 3.5
1.18 30	10 x 24	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.20 30.5	0.14 3.5
1.18 30	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.20 30.5	0.14 3.5
1.77 45	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
1.77 45	10 x 24	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
1.77 45	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
2.48 63	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
2.48 63	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4
3.07 78	1/2 x 13	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	-	-	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4

**Metric table**

Dimensions in: millimeters - inches

l <sub>1</sub>	d <sub>1</sub>	l <sub>2</sub>									d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke
		6	8	10	12	16	-	-	-	-						
30 1.18	M 3	6 0.24	8 0.31	10 0.39	12 0.47	16 0.63	-	-	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14
30 1.18	M 4	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14
30 1.18	M 5	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14
30 1.18	M 6	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	45 1.77	50 1.97	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14
45 1.77	M 4	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14
45 1.77	M 5	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14
45 1.77	M 6	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	45 1.77	50 1.97	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14
63 2.48	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	-	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16
63 2.48	M 8	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	45 1.77	50 1.97	63 2.48	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16
63 2.48	M 10	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	45 1.77	50 1.97	63 2.48	80 3.15	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16
78 3.07	M 8	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16
78 3.07	M 10	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	45 1.77	50 1.97	63 2.48	80 3.15	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16
78 3.07	M 12	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	-	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16