



Specification

- Lever body
Plastic **KT**
Nylon thermoplastic
- Glass fiber reinforced
- With molded-in stainless steel inlay
- Temperature resistant up to 230 °F (110 °C)
- Color
Black, RAL 9005, textured finish **● SW**
Orange, RAL 2004, textured finish **● OS**
Gray, RAL 7035, textured finish **● GS**
- Insert / retaining screw
Steel, blackened finish
- ISO Fundamental Tolerances → page 2129
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Special colors, bores, and threads

Information

Made in the USA, WN 300 adjustable levers are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

All such levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Adjustable Levers WN 300 (Nylon Plastic, Threaded Stud Type) → page 420
- Adjustable Levers GN 300 (Zinc Die-Cast, Tapped or Plain Bore Type) → page 402
- Adjustable Levers WN 303 (Nylon Plastic, with Push Button, Tapped or Plain Bore Type) → page 444
- Adjustable Levers GN 303 (Zinc Die-Cast, with Push Button, Tapped or Plain Bore Type) → page 436

How to order (Inch)	1 Material
WN 300-KT-45-1/4X20-SW	2 Lever length l ₁
	3 Thread d ₁ (Bore d ₂)
	4 Color
How to order (Metric)	1 Material
WN 300-KT-78-B10-GS	2 Lever length l ₁
	3 Bore d ₂ (Thread d ₁)
	4 Color

Inch table

Dimensions in: inches - *millimeters*

l ₁	d ₁ Thread			d ₂ +0.001 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
				B								
1.18 30	10 x 32	10 x 24	1/4 x 20	B 1/4		0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.20 30.5	0.14 3.5	0.35 9
1.77 45	10 x 32	10 x 24	1/4 x 20	B 1/4		0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5	0.35 9
2.48 63	1/4 x 20	5/16 x 18	-	B 5/16		0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4	0.43 11
3.07 78	5/16 x 18	3/8 x 16	-	B 3/8		0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4	0.55 14
3.62 92	3/8 x 16	1/2 x 13	-	B 1/2		0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65	0.16 4	0.67 17

Metric table

Dimensions in: millimeters - *inches*

l ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
				B								
30 1.18	M 3	-	-	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	7 0.28
30 1.18	M 4	M 5	M 6	B 5	B 6	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	9 0.35
45 1.77	M 4	M 5	M 6	B 5	B 6	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14	9 0.35
63 2.48	M 6	M 8	-	B 6	B 8	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16	11 0.43
78 3.07	M 8	M 10	-	B 8	B 10	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16	14 0.55
92 3.62	M 10	M 12	-	B 10	B 12	19 0.75	25.2 0.99	43 1.69	11 0.43	65 2.56	4 0.16	17 0.67

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

