



**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> l <sub>1</sub>	<sup>2</sup> d <sub>1</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	t min.
1.77 45	10 x 32 10 x 24 1/4 x 20	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.35 9
2.48 63	1/4 x 20 5/16 x 18	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.43 11
3.07 78	5/16 x 18 3/8 x 16	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.55 14
3.62 92	3/8 x 16 1/2 x 13	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65	0.67 17

**Specification**

- Lever body  
Nylon thermoplastic
  - Glass fiber reinforced
  - With molded-in stainless steel inlay
  - Temperature resistant up to 230 °F (110 °C)

- Color
  - Black, RAL 9005, textured finish ● **SW**
  - Orange, RAL 2004, textured finish ● **OS**
  - Gray, RAL 7035, textured finish ● **GR**

- Tapped insert / retaining screw  
Steel
  - Blackened finish
  - Not removable, loctited

• Plastic Characteristics → page 2135

• RoHS compliant

**On request**

- With all stainless steel components
- Special inch and metric bores or threads

**Information**

WN 400 fixed clamping levers are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

The solid steel tapped insert allows the operator the ability to apply additional torque where needed to the item being clamped or fastened.

see also...

- Fixed Clamping Levers WN 400 (Threaded Stud Type) → page 543

How to order

<sup>1</sup> <sup>2</sup> <sup>3</sup>  
**WN400-45-10X32-SW**

<b>1</b>	Lever length l <sub>1</sub>
<b>2</b>	Thread d <sub>1</sub>
<b>3</b>	Color