



Inch table

¹ l ₁	² d ₁ Bore	³ h ₂	h ₄	h ₅	h ₁	h ₃	d ₂	l ₂	d ₃ Ø Handle	Handle Thread
3.94 100.1	B 3/8	3.40 86.4	2.56 65.0	7.75 196.9	1.57 39.9	2.10 53.3	0.625 15.9	6.28 159.5	0.98 24.9	M 8

Dimensions in: inches - millimeters

Specification

- Crank body
Nylon plastic
- Glass filled
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Hub bushing
Steel, zinc plated
- Revolving handle
Plastic
Duroplast (Phenolic PF)
- Black, shiny finish
- Threaded spindle
Steel, zinc plated
- Spring loaded retracting mechanism
Steel, zinc plated
- Keyways *WN / DIN 6885* → page XYZ / XYZ
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

On request

- For certain minimum quantities, inch bore sizes from .250”-.506” and metric bore sizes from 6 mm-12 mm
- For certain minimum quantities, square mechanisms can also be manufactured

Information

Retracting hand cranks are just one of many specials that have become a standard product. Can be used in any application requiring the complete crank handle to be folded out of the way. Please call us with your application requirements.

see also...

- *Crank Handles MV-M* → page 284

How to order

¹ ² ³
WRHC-3.94-B3/8-3.40

- | | |
|---|---------------------------|
| 1 | Length l ₁ |
| 2 | Blind bore d ₁ |
| 3 | Height h ₂ |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4