



- 4 Type**
- A 2x2 tapped inserts
 - C 2x2 bores for countersunk screw
 - D 2x2 threaded studs

Metric table

Dimensions in: millimeters - inches

1	2	3		3									
l_1	l_2	d_1 Type A, D		d_2 Type C	d_3	h_1	h_2	h_3	l_3	l_4	$m_1 \pm 0.2$	$m_2 \pm 0.2$	t
40 1.57	40 1.57	-	-	B 4.2	4 0.16	16.5 0.65	10 0.39	11.5 0.45	-	14 0.55	25.5 1.00	25.5 1.00	-
48 1.89	48.1 1.89	M 5	M 6	B 5.5	5 0.20	20.5 0.81	12.5 0.49	14.5 0.57	15 0.59	17 0.67	31 1.22	30 1.18	11 0.43
65 2.56	64.9 2.56	M 6	-	B 6.5	6 0.24	25 0.98	14 0.55	17 0.67	20 0.79	24 0.94	40 1.57	40 1.57	11 0.43
98 3.86	97.8 3.85	M 10	-	B 10.5	8 0.31	37 1.46	21 0.83	25 0.98	20 0.79	35 1.38	63 2.48	60 2.36	11 0.43

Specification

- Body
Nylon plastic
- Glass fiber reinforced
- Black, matte finish
- Pin
Stainless steel AISI 303
- Tapped inserts
Brass, molded-in
- Threaded studs
Steel, zinc plated, molded-in
- *Stainless Steel Characteristics* → page 2143
- RoHS compliant

Information

- An economical, yet very durable, substitute for metal hinges.
- see also...
- *List of Hinge Types* → page 1324
 - *Hinges EN 151 (Technopolymer Plastic)* → page 1347
 - *Lockable Hinges EN 151.2* → page 1421
 - *Hinges EN 151.3 (Technopolymer Plastic)* → page 1348
 - *Hinges EN 151.4 (Technopolymer Plastic)* → page 1406

How to order	
1	Width l_1
2	Length l_2
3	Thread d_1 (Bore d_2)
4	Type

C-40-40-B4.2-C