



**Metric table**

Dimensions in: millimeters - inches

1 d Clamp slot size	2 l <sub>1</sub>	Metric bolt size		b <sub>1</sub>	b <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>
		M 12	M 18					
18 .71	100 3.94	M 12	M 18	40 1.57	20 .79	40 1.57	20 .79	26 1.02
25 .98	140 5.51	M 20	M 24	60 2.36	30 1.18	60 2.36	30 1.18	38 1.50

**Specification**

- Goose neck clamp  
Tempered steel, lacquer painted finish
- RoHS compliant

**Accessory**

- DIN 787 T-slot bolt → page QVX
- DIN 6330 fixture nut → page QVX
- DIN 6340 heavy duty flat washer → page QVX
- DIN 508 T-slot nut → page QVX
- DIN 6379 double-ended threaded stud → page QVX

**Information**

No. 6317 doubled ended goose neck clamps are a great choice when side-by-side or back-to-back clamping of the same or somewhat varied height workpieces need to be clamped.  
DIN 6340 heavy duty flat washers or DIN 6319 spherical washers are typically used with this clamp to achieve the aforementioned clamping options.

see also...

- Heavy Duty Flat Washers DIN 6340 → page QVX
- Spherical Washers DIN 6319 → page QVX

How to order 1 2 <b>NO.6317-25-140</b>	1	Clamp slot size d
	2	Length l <sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

